



# SUPERBLAST AUTOCLAVE

## MULTI-USE AUTOCLAVABLE

The SUPERBLAST AUTOCLAVE range has been specially designed to meet all cleanrooms requirements. Equipped with our exclusive anti-fog and anti-scratch PLATINUM coating on both sides of the lens, our range of autoclavable multi-use goggles are resistant to high temperature and still fully functional after several autoclaving cycles. Our goggles' designs fit over any prescription glasses, ensuring improved eye protection and vision.

- + **OVERFLOW CHUTE FOR LIQUIDS**
- + **UPPER VENTILATION / SEALED IN THE LOWER PART**
- + **COMPATIBLE WITH A HALF-MASK RESPIRATOR**
- + **PLATINUM COATING : ANTI-SCRATCH & ANTI-FOG**



### TECHNOLOGIES

PLATINUM

### VERSIONS



SUPBLCLAVE



SUPBLCLAV2



SUPBLCLAV3

**bollé**  
SAFETY

**SUPERBLAST AUTOCLAVE**

USE	VERSION	REFERENCE	LENS MARKING	FRAME MARKING	COATING	STANDARD
	CLEAR	SUPBLCLAVE	2C-1.2  1 BT KN CE	EN166 3 4 BT CE	PLATINUM	EN166-EN170
	CLEAR	SUPBLCLAV2	2C-1.2  1 BT KN CE	EN 166 BT CE	PLATINUM	EN166-EN170
	CLEAR	SUPBLCLAV3	2C-1.2  1 BT KN CE	EN 166 BT CE	PLATINUM	EN166-EN170

S: MODELS IN SMALL SIZE

**PACKAGING & EAN13 CODE**

SINGLE Size: 355 x 177 x 70 mm	INNER BOX: Size: 34x18x11 cm Weight: 0.72 g	OUTER PACK: Size: 60 x 50 x 37 cm Weight: 37 kg
3660740008239	3 660 740 108 236 -5 pcs	3 660 740 208 233 -65 pcs
3660740008758	3660740108755 -5 pcs	3660740208752 -65 pcs
3660740009304	3660740109301 -5 pcs	3660740209308 -65 pcs
<b>CUSTOM CODE:</b> 9004901000		

**SUPBLCLAVE : GENERAL SPECIFICATIONS**

<b>LENS</b>	POLYCARBONATE
<b>FRAME</b>	TPR - INDIRECT VENTILATED ON THE UPPER PART AND SEALED ON THE BOTTOM
<b>WEIGHT</b>	95 g
<b>STRAP</b>	ISOPRENE - WHITE
<b>USE</b>	MULTI USE - AUTOCLAVE

**SUPBLCLAV2 : GENERAL SPECIFICATIONS**


<b>LENS</b>	POLYCARBONATE
<b>FRAME</b>	TPR - DIRECT VENTILATED ON THE UPPER PART AND SEALED ON THE BOTTOM
<b>WEIGHT</b>	94 g
<b>STRAP</b>	ISOPRENE - WHITE
<b>USE</b>	MULTI USE - AUTOCLAVE

**SUPBLCLAV3 : GENERAL SPECIFICATIONS**

<b>LENS</b>	POLYCARBONATE
<b>FRAME</b>	TPV PROVIDING A HIGHER NUMBER OF CYCLES IN AUTOCLAVE STERILIZATION AT 134° C DIRECT VENTILATED ON THE UPPER PART AND SEALED ON THE BOTTOM -
<b>WEIGHT</b>	97 g
<b>STRAP</b>	ISOPRENE - WHITE
<b>USE</b>	MULTI USE - AUTOCLAVE

**SUPBLCLAVE****SUPBLCLAV2****SUPBLCLAV3**

KNOW MORE ABOUT MARKINGS:



OR SCAN:

**CLEANING & STORAGE**

**CLEANING:** The lenses should be cleaned regularly. Bollé Safety recommends only using the B-clean lens cleaning system.

**MAINTENANCE:** Pitted, scratched or damaged lenses must be replaced by replacing the complete product. If the frame is damaged also replace the complete product. After each use it is recommended to keep the spectacles or goggles in a microfibre pouch or rigid case.

**STORAGE:** All products must be stored in a dry and clean environment.



MADE IN: TW

DATASHEET: 12-14-2021

**bolle-safety.com**

Europe Headquarters  
34 rue de la Soie  
69100 Villeurbanne  
France  
Tél. : 00 33 (0) 4 78 85 23 64

U.K. & Ireland  
Unit C83 - Barwell Business Park  
Leatherhead Road - Chessington  
Surrey - KT9 2NY - UK  
Tél. : 00 44 (0)208 391 4700

USA Office  
2810 Caribou Court, Suite 160  
Carlsbad, CA 92010  
United States of America  
Tél. : 800 222 6553

Asia-Pacific Office  
32-40 Fairchild Street  
heather-ton VIC 3202  
Australia  
Tél. : 1300 138 098

**THE PPE EYEWEAR SPECIALISTS**